

VP Ultra 2.0,
multi-purpose progressive
lens with excellent results in
user tests:

VP Ultra 2.0



9/10 USERS ADAPT TO THE
PROGRESSIVE IN THE
FIRST HOURS OF USE

Patients that demand personalized
lenses.

Those looking for the best
performance in any environment.
Recommended when using hand
held devices.

VP Ultra 2.0

92% OF USERS RATE THE
VISUAL EXPERIENCE
AS VERY SATISFACTORY

Progressive lens
with a unique gene



(* Test performed to progressive wearers
who work daily with computer (74% of cases)
and drive regularly (68%).



VP Ultra 2.0

4286 Mt. Carmel-Tobasco Rd., Suite E
Cincinnati, Ohio 45244 | **Tel:** 513-273-4034

www.RandOptical.com

R & D 
OPTICAL LAB
CUTTING EDGE TECHNOLOGY

VP Ultra 2.0

progressive lens has a unique gene because its calculation includes ClearView optimization technology.



Standard progressive has an intense concentration of blurriness in the peripheral areas, can disturb and can cause discomfort to the user.



INGENIOUS provides maximum clear vision thanks to the minimization of the lateral blurriness that results in an improvement of the visual comfort.

VP Ultra 2.0

innovation in progressive lenses

ClearView

Panoramic, clear vision

OptiMesh

Lens is optimized according to the position of wear

DIGITAL PROFILE

Progressive lens is designed to cover the vision demands of hand held devices wearers

Variable Inset

Selection of the inset for an optimal reading area

Variable Corridor

Selection of the optimal corridor according to the chosen frame

VP Ultra 2.0

the best performance for demanding users:



Wide & clear fields of vision



Personalized lens that considers the real position of wear



Adapted to the digital world



ThinMax option available



VISUAL
PERFECTION 2.0